

Sophisticated new functions for Spectrum's measurement software

Spectrum Instrumentation adds customization, automation and interpolation capabilities to its powerful SBench 6 software

Grosshansdorf, Germany - December 3th, 2020. A number of new functions have been added to SBench 6-Professional, the software that is used for controlling Spectrum Instrumentation's 130 different high-performance digitizers, 55 different Arbitrary Waveform Generators and 5 Digital I/O products. SBench 6 provides an easy-to-use graphical interface for instrumentation control as well as data acquisition, generation, display, analysis and documentation. The new features, most of them free of charge, expand the versatility of the software by adding functionality for automation as well as increasing the software's capabilities for signal processing and measurement precision.

Scripting allows easy automation

For users who want a simple way to utilize SBench6 in an automated sequence of operations, a scripting tool is now available. Scripting allows basic commands to be arranged via a plain ASCII file that is called by the SBench 6 program. For example, SBench 6 can be instructed to load specific configurations, start and stop acquisitions, wait or loop, export data and even call external programs (see Figure 1).

```
# do an acquisition 10 times every minute and export to MATLAB file format
SB6_LOOP_START 10
  SB6_START SINGLE
  SB6_EXPORT_DATA MATLAB C:/MyMatlabExport/myTestData.mat
  SB6_WAIT_SEC 60
SB6_LOOP_END
```

Figure 1 shows a small ASCII script file that asks SBench 6 to make ten acquisitions each minute and export the data produced directly to MATLAB.

Improve accuracy of measurements with data interpolation

Another useful addition to the SBench 6-Professional software is data interpolation. This powerful feature can be used to dramatically improve parameter measurements in situations where the sampling rate of a digitizer is limiting measurement precision. Based on the SinX/x (or sometimes called SinX) algorithm, the SBench 6 interpolation function inserts samples in a predictive manner between the actual acquired data points. When done correctly, this produces a waveform with a higher effective sampling rate and a closer approximation to the analogue waveform that is being analyzed.

The benefit of interpolation becomes apparent as the input signal frequency begins to approach the Nyquist limit (half the sampling rate). Consider figure 3. Here a 20 MHz sine wave with 1.82 V amplitude is acquired by a digitizer sampling at 125 MS/s and with 16-bit resolution. The yellow trace on the left shows the signal without interpolation and with the sample points connected by linear lines. The blue trace on the right is the same signal but with interpolation activated. Both traces have been expanded vertically so you can examine the top of the sine wave.




Figure 3. Interpolation can significantly improve parameter measurement accuracy and precision.

Headquarters

Spectrum Instrumentation GmbH, Germany
 Phone: +49 4102-6956-0
 Email: Info@spec.de

US Office

Spectrum Instrumentation Corp., USA
 Phone: (201) 562-1999
 Email: Sales@spectrum-instrumentation.com

Note that the 20 MHz signal is still well below the Nyquist limit of 62.5 MHz. However, the yellow trace (without interpolation) already has an insufficient sampling rate to precisely measure the signal's amplitude. The problem is that, at 125 MS/s, each cycle of the sine wave only contains around six sample points. Activating the interpolation function effectively improves the sampling rate. In this example, an interpolation factor of 10 was selected, creating a trace with 60 samples per cycle. Parameter measurements for the Peak-to-Peak amplitude (lower left corner) made for both traces show the significant improvement in amplitude accuracy that is possible.

Providing the frequency content of the input signal does not exceed the Nyquist limit, interpolation can be also be used to improve other parameter measurements (such as rise and fall times, as well as cyclic measurements like frequency and period).

Perform Customized Calculations

SBench 6-Professional has an extensive array of data processing tools (e.g. FFT analysis, math functions, filtering, averaging, parameter measurements, etc.) that can now be complimented by a new plug-in option which enables users to create their own customized calculations as a self-compiled plug-in that is automatically linked into the SBench 6 calculation pool. The plug-in option includes an SDK as well as a number of examples based on the C++ programming language. It allows programmers to develop their own plug-ins by combining advanced calculations on the acquired signals. Any calculation that can be realized with standard development




Figure 2. A Plug-in example for signal inversion with customized data storage.

methods is possible. Furthermore, any files in the system (such as filter parameters, sensor calibration values or reference signals) can be utilized in the calculation. The SDK also provides a call-back function for interaction with the user so that simple dialogs and other information, such as cautions or critical warnings, can then be flagged to the user.

The plug-in option allows users to integrate their own processing functions directly into the SBench 6 program. Resulting signals can be displayed, used for further calculations, exported or can be part of a report. For example, when using a digitizer together with sensors, the plug-in could embed specific sensor calibration information into the program. Figure 2 shows a typical plug-in example where signals are inverted and stored. Note that programmer can define the calculation configuration using integer or double values, combo boxes, strings or

checkboxes.

Programming custom calculation routines can turn SBench 6 software into a powerful application specific tool. Once the routines are developed, the resulting plug-in files can be freely distributed with any SBench 6 Professional license to end-users.

Calculate Single Values

As part of the SBench 6 enhanced measurement capabilities, it is now also possible for the new Formula function to calculate single values. These values can be computed from the cursor information, any sample of a source signal or even from other calculation results.

Adding to the processing flexibility, "single values" can even be accessed and incorporated into a formula when creating new waveforms with the program's Function Generator feature. The result is a waveform creation tool that lets you make waveforms using recorded or loaded signals, an extensive list of mathematical operations and single values!

Detect out-of-range signals with Input Channel Preview

To make setting-up the input ranges of a digitizer fast and easy, an Input Channel Preview window has been

Headquarters

Spectrum Instrumentation GmbH, Germany
 Phone: +49 4102-6956-0
 Email: Info@spec.de

US Office

Spectrum Instrumentation Corp., USA
 Phone: (201) 562-1999
 Email: Sales@spectrum-instrumentation.com

added to SBench 6-Professional. The window works by continuously monitoring the input signals at a low sampling rate and then displaying their key signal characteristics using a bar graph. The Input Channel Preview window reveals, for each active channel, the signal's current minimum, maximum and average value. Color coding (green, red and yellow) then highlights when signals are in and out of range or when an input range has changed status. Users are instantly alerted to each channel's condition, making it immediately obvious when changes to the setting of their gain or offset may be required.

Free for all SBench6-Professional Users

With the exception of the Plug-in tool for customized calculations, which is an option, customers already using SBench 6-Professional can access the new capabilities (Scripting, Single Value Formula, Input Channel Preview and Interpolation) for free. The functions, along with other recent additions to the program, such as FFT based Power Spectrum Density measurements, can be obtained simply by downloading the latest version of the software directly from the Spectrum Instrumentation website (www.spectrum-instrumentation.com). A free trial version of SBench 6-Professional is also available for anyone wishing to test the program's capabilities. The program runs with simulated hardware to allow users to get a full understanding of how it operates. The website also offers a new series of "How to do" videos for your quick start into the basic functions of SBench 6.

About Spectrum Instrumentation

Spectrum Instrumentation, founded in 1989, uses modular design to create a wide range of digitizer and generator products as PC-cards (PCIe and PXIe) and stand-alone Ethernet units (LXI). In 30 years, Spectrum has gained customers all around the world, including many A-brand industry-leaders and practically all prestigious universities. The company is headquartered near Hamburg, Germany, and known for its outstanding support that comes directly from the design engineers. More information about Spectrum can be found at www.spectrum-instrumentation.com

Headquarters

Spectrum Instrumentation GmbH, Germany
Phone: +49 4102-6956-0
Email: Info@spec.de

US Office

Spectrum Instrumentation Corp., USA
Phone: (201) 562-1999
Email: Sales@spectrum-instrumentation.com

<https://www.spectrum-instrumentation.com>